

- 1: Lift eye location (M12 threaded nutsert) @ 2 per display
- 2: Section ventilation
- 3: Door hardware location

Figure 1: Display (Front View)






Figure 5: Component Access



- 1: Clip
- **2:** Seam
- 3: One M12 bolt in the top slot for top row clips
- 4: One M12 bolt in each slot for spanning clips
- 5: One M12 bolt in the bottom slot for bottom row clips


Figure 2: Display (Rear View)



- 1: Fiber Converte
- 2: ProLink Router (PLR), configurable & not found in every cabinet
- 3: Junction Box
- **4:** Power Supply (@3 per cabinet with bulk power supply; @5 per cabinet with Meanwell power supply
- 5: Power Entrance
- 6: Signal Entrance
- 7: Optional Signal Entrance


Figure 6: Component Locations (Rear View)

201 Daktronics Drive Brookings, SD 57006-5128 www.daktronics.com/support 800.325.8766



- 1: Corner block @ 4 per display
- 2: Interconnect hardware location (M6 bolt & nutsert) @ 1 per corner block (center location)

Figure 3: Corner



- 1: Vertical mounting clip location (M12 threaded nutsert) @ 4 per section
- 2: Horizontal mounting clip location (M12 threaded nutsert) @ 4 per section

Figure 4: Mounting Clip Attachment Points